


# Mobile Phone Keypad Test using Agilent USB Data Acquisition Device



## Application Note



### Contents

Introduction	1
Keypad Test	1
Conclusion	3

### Introduction

Mobile phones have been an essential gadget for the past few years and users come from all levels of ages. In an attempt to attract costumers, mobile phone manufacturers have reduced the size of mobile phones tremendously and this leads to smaller numeric keypads.

These numeric keypads are tested to ensure their ease of use. One important measurement is the force on the keypad. In order to meet the force specification, the force should be sufficiently low, but not too low to avoid accidental activation of the keypad.


### Keypad Test

A basic keypad test system consists of a universal test machine. It is equipped with a low capacity force sensor fixed on the test arm. In addition, a T-slot table is used to support the phone or keypad module. In this test, the prong will simulate the motion when a mobile phone user presses a button on the keypad. During this test, the load profile and displacement characteristic of the keypad are monitored.

For more detailed information, the test system can include electrical contact measurement. This test result would then provide precise measurement for the switch closure position and force. A system with high data logging capability is recommended. This to enable observation of rapid changes in force, which may occur at very small distances between switch closures.

An example of the keypad test system is illustrated in Figure 1.





**Figure 1** Keypad test system

In this setup, the device under test (DUT) is the mobile phone. The force sensor is used to measure the force that is used to press the button on the keypad. The force sensor converts this measured force to a voltage output and sends it to the signal conditioner. The signal conditioner amplifies the voltage and filters out any unnecessary noise. The filtered signal is sent to a DAQ device for more accurate measurements. The DAQ device then collects these data and sends the data to PC for display and post processing.

An example of a force sensor is the piezoelectric force sensor. Force, like any other type of physical measurement, cannot be measured without disturbing the measurement. Most force sensors have an elastic sensing part, where its deformation is the measurement of the acting force. The elastic sensing part must be sensitive and able to go through sufficient deformation.

A large deformation is not preferable as it limits the frequency response of the system and increases measurement errors due to the introduction of geometric changes into the force measuring path. Examples of such errors are linearity and hysteresis. In piezoelectric force transducers, the sensing part is the same as the transduction part, which produces electrical output from an acting force. Therefore, measurement of the deformation is not necessary since it is much smaller when used with other measuring systems.

The geometric disturbance caused by the test is reduced by the high rigidity of piezoelectric force sensors. The high rigidity also provides high natural frequency and rise time. This allows measurement of shock waves in solids, impact printer and punch press force.

The force sensor is attached to the test arm. Only the downward force is measured since this simulates the pressing of the keypad. The force sensor converts this force to a corresponding DC voltage output.

The actual force measured can be easily calculated. If the sensitivity of the force sensor is 20 mV/N and the amplification of the signal conditioner is 10 times, this gives an actual measured reading of 100 mV and actual force of 0.5 N.

This type of test system is well suited for monitoring data over a long period of time. Hence, the PC is an ideal data-collection point in this test system as it comes with relatively deep memory storage.

The Agilent USB DAQ device offers a low switching cost as the PC comes with standard USB ports. The plug-and-play feature of the USB connectivity simplifies setup and increases the DAQ device's functionality.

### **Conclusion**

There is a need for a test system that is able to acquire and store a lot of data. Ease of use and low switching cost are advantages that can decrease the cost of developing mobile phones. This will then help to offer a more competitive pricing for customers. The Agilent USB DAQ device with its interface to PC, poses itself as the ideal solution to the above testing needs.

Visit [www.agilent.com/find/U2300A](http://www.agilent.com/find/U2300A) for additional information or contact your nearest Agilent sales office or sales representative.

**www.agilent.com**  
**800 123-4567**



## **Agilent Email Updates**

[www.agilent.com/find/emailupdates](http://www.agilent.com/find/emailupdates)

Get the latest information on the products and applications you select.

### **Agilent T&M Software and Connectivity**

Agilent's Test and Measurement software and connectivity products, solutions and developer network allows you to take time out of connecting your instruments to your computer with tools based on PC standards, so you can focus on your tasks, not on your connections.

Visit [www.agilent.com/find/connectivity](http://www.agilent.com/find/connectivity) for more information.

**By internet, phone, or fax, get assistance with all your test & measurement needs.**

### **Online assistance:**

[www.agilent.com/find/assist](http://www.agilent.com/find/assist)

Phone or Fax

#### **United States:**

(tel) 800 829 4444

(fax) 800 829 4433

#### **Canada:**

(tel) 877 894 4414

(fax) 800 746 4866

#### **China:**

(tel) 800 810 0189

(fax) 800 820 2816

#### **Europe:**

(tel) (31 20) 547 2111

(fax) (31 20) 547 2390

#### **Japan:**

(tel) (81) 426 56 7832

(fax) (81) 426 56 7840

#### **Korea:**

(tel) (82 2) 2004 5004

(fax) (82 2) 2004 5115

#### **Latin America:**

(tel) (650) 752 5000

#### **Taiwan:**

(tel) 0800 047 866

(fax) 0800 286 331

#### **Other Asia Pacific Countries:**

(tel) (65) 6375 8100

(fax) (65) 6836 0252

Email: [tm\\_ap@agilent.com](mailto:tm_ap@agilent.com)

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2006  
Printed in USA, November 15, 2006  
5989-5777EN



**Agilent Technologies**